

# LENS WIPES #4161301

Premoistened Lens Cleaning Wipes



## Features:

- Effectively cleans eyeglasses, safety glasses, binoculars, plexiglass & other optical surfaces
- Anti-static & anti-fog
- Fast evaporating formula
- Size: 6" x 7"
- 100 wipes per canister

## Description:

LENS WIPES are premoistened towelettes that contain a specifically formulated Lens Cleaning Solution. These wipes clean dirt, grease, and oils from optical surfaces. The formula also contains anti-fog and anti-static additives for a fast-evaporating formula. The 6"x7" wipes are perfect for cleaning any optical equipment surface.



## Applications:

- Safety Glasses
- Eye Glasses
- Binoculars
- Plexiglass

## Product Characteristics:

Appearance:	Premoistened wipe
Physical State:	Solid
Odor:	Mild odor
Viscosity:	No data available
Vapor Pressure:	No data available
Solubility:	Liquid component is soluble in water
Relative Density:	No data available
VOC Content:	< 3% Tested using the liquid component of the towelette
Flash Point:	132°F Closed cup - Tested using the liquid component of the towelette
pH:	9 – 10 Tested using the liquid component of the towelette
Storage:	Keep container closed when not in use.
<b>Transport Information:</b>	
UN Number:	Not regulated for transport
Proper Shipping Name:	Not regulated for transport
Class:	Not regulated for transport
Packing Group:	Not regulated for transport

## Directions For Dispensing:

1. Remove lid by lifting upward. Remove foil seal.
2. Pull towel from center of the roll and thread through "X" on the underside of the lid.
3. Close lid. Pull towel at 90° angle.
4. Snap hinged cap back into place to ensure towels stay moist.

**\*Do not flush.**

## Pictograms:



## Signal Word:

Warning

## Personal Protective Equipment Required:



## DOT Placard:

Not available.

## VOC Compliancy:

Not available.